

**ZQV 4N/30 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Order No.	<a href="#">256160000</a>
Type	ZQV 4N/30 RD
GTIN (EAN)	4050118569964
Qty.	5 Stück

## ZQV 4N/30 RD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	27.95 mm	Depth (inches)	1.1 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	181.7 mm	Width (inches)	7.154 inch
Net weight	22.268 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
Operating temperature, min.	-60 °C	Operating temperature, max.	130 °C
Continuous operating temp., min.	-60	Continuous operating temp., max.	130

### Material data

Material	Wemid	Colour	red
UL 94 flammability rating	V-0		

### Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

### Cross-connector

Number of cross-connected terminals	30	Rated current, 2-pole	32 A
Rated current, multi-pole	32 A	Type	Cross-connector

### Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

### General

Number of poles	30
-----------------	----

### Rating data

Rated current	32 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Important note

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used

### Approvals

ROHS	Conform
------	---------

## ZQV 4N/30 RD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a> <a href="#">BPZL ZQV 2.5</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>