

IE-USB-3.0-A-A-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 5 m
Order No.	2581730050
Type	IE-USB-3.0-A-A-5M
GTIN (EAN)	4050118630558
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 11:13:58 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-USB-3.0-A-A-5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	220 g		

Temperatures

Operating temperature	-15 °C...80 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	80 °C		

Technical specifications for cable

Sheathing colour	blue
------------------	------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)	Material sheath	PVC
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Sheathing colour	blue		

Plug

Plug	Cable side	left
	Version of contact face	USB A 3.0
	Protection degree (IP)	IP20
	Gender of contact	male contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
	Status indicator available	No
	Shielding available	Yes
	Cable side	right
	Version of contact face	USB A 3.0
	Protection degree (IP)	IP20
	Gender of contact	male contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
Status indicator available	No	
Shielding available	Yes	
Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded	
Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded	

Plug, left

Connector left	USB A 3.0	Contact surface, plug, left	Gold over nickel
Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded		

IE-USB-3.0-A-A-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Plug, right

Connector right	USB A 3.0	Contact surface	Gold over nickel
Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded		

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--