

## CD-BO 60X200 8/12 GY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

### General ordering data

Version	Cable duct, 60 mm x 200 mm, 8.00 mm x 12.00 mm, 2000 mm
Order No.	<a href="#">2589010000</a>
Type	CD-BO 60X200 8/12 GY
GTIN (EAN)	4050118602760
Qty.	8 m

Erstellungs-Datum June 1, 2023 10:14:25 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## CD-BO 60X200 8/12 GY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Height	60 mm	Height (inches)	2.362 inch
Width	200 mm	Width (inches)	7.874 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	1,700 g		

### Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

### General information

Colour	grey	Flexible wiring duct	No
Floor rails	3	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Slit gap	12 mm
Slit width	8 mm	Standards	In accordance with DIN EN 50085
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	10,820 mm <sup>2</sup>	Version of side panel	slotted

### Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

### Downloads

Catalogues [Catalogues in PDF-format](#)

**Datenblatt**

**CD-BO 60X200 8/12 GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

