

CD-BO 80X80 4/6 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct floor duct, 80 mm x 80 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2589550000
Type	CD-BO 80X80 4/6 GY
GTIN (EAN)	4050118601206
Qty.	24 m

Erstellungs-Datum June 1, 2023 10:27:33 AM CEST

CD-BO 80X80 4/6 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	80 mm	Height (inches)	3.15 inch
Width	80 mm	Width (inches)	3.15 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	625 g		

Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

General information

Colour	grey	Flexible wiring duct	No
Floor rails	1	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Slit gap	6 mm
Slit width	4 mm	Standards	In accordance with DIN EN 50085
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	5,695 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Catalogues [Catalogues in PDF-format](#)

Datenblatt

CD-BO 80X80 4/6 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

