


**S-4L+9-1000/16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

4-pole pin-type phase distribution bars are used for potential distribution to other components in the control cabinet such as circuit breakers, residual current circuit breakers and other installation devices.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Order No.  | <a href="#">2658920000</a> |
| Type       | S-4L+9-1000/16             |
| GTIN (EAN) | 4050118671605              |
| Qty.       | 5 Stück                    |

## S-4L+9-1000/16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 20.2 mm  | Depth (inches)  | 0.795 inch |
| Height     | 27.5 mm  | Height (inches) | 1.083 inch |
| Width      | 1,016 mm | Width (inches)  | 40 inch    |
| Net weight | 755 g    |                 |            |

### Material data

|        |      |
|--------|------|
| Colour | grey |
|--------|------|

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 17.8 mm |
|-----------------|---------|

### General

|                 |    |
|-----------------|----|
| Number of poles | 48 |
|-----------------|----|

### Rating data

|                     |                    |               |      |
|---------------------|--------------------|---------------|------|
| Rated cross-section | 16 mm <sup>2</sup> | Rated current | 80 A |
|---------------------|--------------------|---------------|------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

### Approvals

Approvals



ROHS Conform

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">CE Declaration of Conformity</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>     |

**Datenblatt**

**S-4L+9-1000/16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Drawing**

