

**CB 430/4,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Version	Cable ties, 4.5 x 430 mm, Polyamide 66, 220 N
Order No.	<a href="#">7940006060</a>
Type	CB 430/4,5 NC
GTIN (EAN)	403224852025 1
Qty.	100 Stück

Erstellungs-Datum June 1, 2023 11:26:39 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## CB 430/4,5 NC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.059 inch
Height	430 mm	Height (inches)	16.929 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	2.92 g		

### Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

### Installation materials

Bundle diameter, max.	115 mm	Bundle diameter, min.	3.5 mm
Cable diameter, max.	115 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

### Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DE PI830000160627_002</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CB 430/4,5 NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

