

SRC 2CO PCB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image**General ordering data**

Version	RIDERSERIES RCL, Flange-mounted housing, Number of contacts: 2, CO contact, Continuous current: 12 A, Print connection
Order No.	8690850000
Type	SRC 2CO PCB
GTIN (EAN)	4032248361533
Qty.	100 Stück

Erstellungs-Datum June 1, 2023 11:56:21 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

SRC 2CO PCB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	9 mm	Height (inches)	0.354 inch
Width	12.7 mm	Width (inches)	0.5 inch
Length	31 mm	Length (inches)	1.22 inch
Net weight	3.34 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

Load side

Rated switching voltage	250 V AC	Continuous current	12 A
Max. switching voltage, AC	300 V	AC switching capacity (resistive), max.	3000 VA
Contact type	2 CO contact		

General data

Colour	black
--------	-------

Insulation coordination

Rated voltage	300 V	Pollution severity	2
Dielectric strength, Input/Output	2.5 kV _{eff} / 1 Min.	Dielectric strength of neighbouring contacts	2.5 kV _{eff} / 1 Min.
Dielectric strength of open contact	1 kV _{eff} / 1 min	Protection degree	IP20

Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

Connection data

Wire connection method	Print connection	Pitch in mm (P)	5 mm
------------------------	------------------	-----------------	------

Classifications

ETIM 6.0	EC001456	ETIM 7.0	EC001456
ETIM 8.0	EC001456	ECLASS 9.0	27-37-16-03
ECLASS 9.1	27-37-16-03	ECLASS 10.0	27-37-16-03
ECLASS 11.0	27-37-16-03	ECLASS 12.0	27-37-16-03

SRC 2CO PCB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223759

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

SRC 2CO PCB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Dimensional drawing

