

IE-XM-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert

General ordering data

Version	Mounting flange, Coupling flange, straight, Cat. 6A, IP67
Order No.	8808450000
Type	IE-XM-RJ45/RJ45-IP67
GTIN (EAN)	4032248506033
Qty.	1 pc(s).

Creation date February 15, 2023 4:35:52 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

IE-XM-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	42 g
------------	------

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Connection 1	RJ45	Connection 2	RJ45
Description of article		Configuration	and RJ45 module, socket-socket captive lid
	Coupling flange, straight		
Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Category	Cat. 6A	Contact surface	Gold over nickel
Type of mounting	Cabinet, Distribution box	Shielding	360°; shield contact
Protection degree	IP67	Plugging cycles	750

General standards

Certificate No. (DNVGL)	TAE00003EW	Connector standard	IEC 61076-3-106 Var. 6, IEC 60603-7-5
-------------------------	------------	--------------------	---------------------------------------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-XM-RJ45/RJ45-IP67

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

