

**SRC-I CLIP HP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Retaining clip for RIDERSERIES RCI relays

- Metal and plastic retaining clip

**General ordering data**

|            |                                 |
|------------|---------------------------------|
| Version    | RIDERSERIES RCI, Retaining clip |
| Order No.  | <a href="#">8869510000</a>      |
| Type       | SRC-I CLIP HP                   |
| GTIN (EAN) | 40322486 14462                  |
| Qty.       | 10 Stück                        |

## SRC-I CLIP HP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 45.6 mm | Depth (inches)  | 1.795 inch |
| Height     | 16.6 mm | Height (inches) | 0.654 inch |
| Width      | 15.5 mm | Width (inches)  | 0.61 inch  |
| Net weight | 1.92 g  |                 |            |

### Temperatures

|                             |  |                             |                |
|-----------------------------|--|-----------------------------|----------------|
| Storage temperature         | -40 °C...85 °C                                 | Operating temperature       | -40 °C...70 °C |
| Operating temperature, min. | -40 °C   | Operating temperature, max. | 70 °C          |
| Humidity                    | 40 °C / 93 % rel. humidity,<br>no condensation |                             |                |

### General data

|         |                 |          |         |
|---------|-----------------|----------|---------|
| Version | for high relays | Material | Plastic |
| Colour  | orange          |          |         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002586    | ETIM 7.0    | EC002586    |
| ETIM 8.0    | EC002586    | ECLASS 9.1  | 27-37-16-92 |
| ECLASS 10.0 | 27-37-16-92 | ECLASS 11.0 | 27-37-16-92 |
| ECLASS 12.0 | 27-37-16-92 |             |             |

### Approvals

Approvals



ROHS Conform

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**SRC-I CLIP HP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Dimensional drawing**

