


## SRC 1CO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Product image



Similar to illustration

### General ordering data

Version	RIDERSERIES RCL, Relay socket, Number of contacts: 1, CO contact, Screw connection
Order No.	<a href="#">8690840000</a>
Type	SRC 1CO
GTIN (EAN)	4032248361526
Qty.	10 Stück

Erstellungs-Datum June 1, 2023 11:56:12 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## SRC 1CO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	61 mm	Depth (inches)	2.402 inch
Height	77 mm	Height (inches)	3.031 inch
Width	15.5 mm	Width (inches)	0.61 inch
Net weight	39.9 g		

### Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

### Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

### Load side

Contact type	1 CO contact
--------------	--------------

### General data

Rail	TS 35	Colour	black
------	-------	--------	-------

### Insulation coordination

Dielectric strength, Input/Output	2.5 kV <sub>eff</sub> / 1 Min.	Dielectric strength of neighbouring contacts	2.5 kV <sub>eff</sub> / 1 Min.
Protection degree	IP20		

### Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

### Connection data

Wire connection method	Screw connection	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.8 Nm	Blade size	size PH1
Pitch in mm (P)	3.5 mm		

### Classifications

ETIM 6.0	EC001456	ETIM 7.0	EC001456
ETIM 8.0	EC001456	ECLASS 9.0	27-37-16-03
ECLASS 9.1	27-37-16-03	ECLASS 10.0	27-37-16-03
ECLASS 11.0	27-37-16-03	ECLASS 12.0	27-37-16-03

## SRC 1CO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223759

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>