

H1,5/14D SW BD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 10 mm, 8 mm, black |
| Order No. | 9004350000 |
| Type | H1,5/14D SW BD |
| GTIN (EAN) | 4008 190005474 |
| Qty. | 500 pc(s). |
| Packaging | Reel packaged |

Creation date March 3, 2023 9:13:15 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H1,5/14D SW BD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.114 g

Technical data

| Description of article | Linked wire-end ferrules, black | Version | Standard |
|------------------------|---------------------------------|---------|----------|
| | | | |

Wire-end ferrules

| | | | |
|---|---------------------|-------------------------------|-------------|
| Collar diameter (D2) | 3.5 mm | Colour code | DIN |
| Conductor cross-section | 1.5 mm ² | Contact surface diameter (D1) | 1.7 mm |
| Contact surface length (L2) | 8 mm | L1 in mm | 14 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Military designation | T 20A 012 A |
| Plastic collar thickness (S2) | 0.25 mm | Stripping length | 10 mm |
| Wire connection cross section AWG, max. | AWG 16 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H1,5/14D SW BD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

