


H6,0/23 ZH SW SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Twin wire-end ferrule, 20 mm, 12 mm, black |
| Order No. | 9004930000 |
| Type | H6,0/23 ZH SW SV |
| GTIN (EAN) | 4008 190482701 |
| Qty. | 100 pc(s). |
| Packaging | Multipack bag |

Creation date March 6, 2023 9:36:48 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H6,0/23 ZH SW SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.69 g

Technical data

| Description of article | Twin wire end ferrule, black | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|
|------------------------|------------------------------|---------|-----------------------|

Wire-end ferrules

| | | | |
|---|------------|-----------------------------|-------------------|
| Collar height (A) | 11.4 mm | Collar width (B) | 6.2 mm |
| Colour code | Weidmüller | Conductor cross-section | 6 mm ² |
| Contact surface diameter (D1) | 4.5 mm | Contact surface length (L2) | 12 mm |
| L1 in mm | 23 mm | Metal sleeve thickness (S1) | 0.2 mm |
| Plastic collar thickness (S2) | 0.5 mm | Stripping length | 20 mm |
| Wire connection cross section AWG, max. | AWG 10 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H6,0/23 ZH SW SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

