

**CTX 500****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Crimping tools for coaxial connectors**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	<a href="#">9006320000</a>
Type	CTX 500
GTIN (EAN)	4008190171049
Qty.	1 pc(s).
Replacement parts	<a href="#">1121010000</a>

## CTX 500

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Net weight	651.08 g		

## Technical data

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 10.54	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

## Description of contact

Type of contact	Coaxial connector
-----------------	-------------------

## tool data crimping

Crimping station, width (B 1)	12 mm	Crimping station, width (B 2)	3.17 mm
Crimping type/profile	Hexagonal crimp	Diameter of outer sleeve	12.2 mm
Hexagon AF (A)	10.54 mm	Hexagon spanner width (A 2)	2.54 mm
Internal contact diameter (D)	2.9 mm		

## Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

## Approvals

Approvals



## Downloads

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**CTX 500**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

**Drawings**

