

PZ 16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² , Indent crimp
Order No.	9012600000
Type	PZ 16
GTIN (EAN)	4008 190035440
Qty.	1 pc(s).
Replacement parts	9012640000 9202810000

Creation date February 15, 2023 5:02:38 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

PZ 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	429.8 g		

Technical data

Description of article	(2)Crimping tool	Version	Mechanical, without interchangeable inserts
------------------------	------------------	---------	---

Description of contact

Conductor cross-section, min. AWG	AWG 10	Crimping range, max.	16 mm ²
Crimping range, min.	6 mm ²	Type of contact	Wire-end ferrules with/without plastic collars

tool data crimping

Crimping profile 1, min.	6 mm ²	Crimping profile 2, min.	10 mm ²
Crimping profile 3, min.	16 mm ²	Crimping type/profile	Indent crimp
Wire end ferrules cross-section, max.	16 mm ²	Wire end ferrules cross-section, min.	6 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

PZ 16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

