

**HTF SUB-D****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Crimping tools for SUB-D contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, FoderBcrimp
Order No.	<a href="#">9013260000</a>
Type	HTF SUB-D
GTIN (EAN)	4008190056896
Qty.	1 pc(s).

**HTF SUB-D**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	440.98 g		

**Technical data**

Description of article	Crimping tools for SUB-D contacts, AWG 28-20	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

**Description of contact**

Conductor cross-section, min. AWG	AWG 28	Type of contact	SUB-D
-----------------------------------	--------	-----------------	-------

**tool data crimping**

Crimping profile 1, max.	24 AWG	Crimping profile 1, min.	28 AWG
Crimping profile 2, max.	20 AWG	Crimping profile 2, min.	22 AWG
Crimping type/profile	FoderBcrimp		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Approvals**

Approvals



**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**HTF SUB-D**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

**Drawings**

