

H6,0/26D GE**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 20 mm, 18 mm, yellow |
| Order No. | 9019230000 |
| Type | H6,0/26D GE |
| GTIN (EAN) | 4008190072117 |
| Qty. | 100 pc(s). |
| Packaging | loose |

H6,0/26D GE

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

| | | |
|------------|-------|---------------------|
| Net weight | 0.5 g | www.weidmueller.com |
|------------|-------|---------------------|

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule with plastic collar, yellow | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|---|-------------------|-------------------------------|-------------|
| Collar diameter (D2) | 6.3 mm | Colour code | DIN |
| Conductor cross-section | 6 mm ² | Contact surface diameter (D1) | 3.5 mm |
| Contact surface length (L2) | 18 mm | L1 in mm | 26 mm |
| Metal sleeve thickness (S1) | 0.2 mm | Military designation | T 20A 023 A |
| Plastic collar thickness (S2) | 0.3 mm | Stripping length | 20 mm |
| Wire connection cross section AWG, max. | AWG 10 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H6,0/26D GE

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings

Drawing

