

**LIF 1,5F488 R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated tab-connector sleeves made from PVC  
with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

**General ordering data**

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> , 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
Order No.	<a href="#">9200530000</a>
Type	LIF 1,5F488 R
GTIN (EAN)	40322484 10378
Qty.	100 pc(s).

Creation date February 23, 2023 10:58:54 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## LIF 1,5F488 R

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5.7 mm	Depth (inches)	0.224 inch
Width	19.2 mm	Width (inches)	0.756 inch
Net weight	0.71 g		

## Technical data

Description of article	Insulated tab-connector sleeves 1.5 mm <sup>2</sup> / 4.8x0.8
------------------------	---

## Connectors

Conductor cross-section	1.5 mm <sup>2</sup>	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	Dimension	4.8 x 0.8 mm
Dimension (flat blade connector)	4.8 x 0.8 mm	Identification colour	red
Insulation	Available	Material/plastic	PVC
Plastic collar diameter (D)	4 mm	Plastic collar length (b)	10 mm
Plug-in density (d3)	0.8 mm	Plug-in width (d2)	4.8 mm

## Classifications

ETIM 6.0	EC0005 16	ETIM 7.0	EC0005 16
ETIM 8.0	EC0005 16	ECLASS 9.0	27-44-03-92
ECLASS 9.1	27-40-02-90	ECLASS 10.0	27-44-03-92
ECLASS 11.0	27-44-03-92	ECLASS 12.0	27-44-03-92

## Approvals

Approvals



ROHS

Conform

## Downloads

Catalogues [Catalogues in PDF-format](#)

Brochures

**Data sheet**

**LIF 1,5F488 R**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

