


## H16,0/29 ZH GN

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 20 mm, 16 mm, green
Order No.	<a href="#">9037360000</a>
Type	H16,0/29 ZH GN
GTIN (EAN)	4008 190492830
Qty.	50 pc(s).
Packaging	loose

Creation date February 17, 2023 11:49:34 AM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**H16,0/29 ZH GN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 1.38 g

**Technical data**

Description of article	Twin wire end ferrule, green	Version	Twin wire-end ferrule
------------------------	------------------------------	---------	-----------------------

**Wire-end ferrules**

Collar height (A)	17.2 mm	Collar width (B)	9.5 mm
Colour code	Weidmüller	Conductor cross-section	16 mm <sup>2</sup>
Contact surface diameter (D1)	8.3 mm	Contact surface length (L2)	16 mm
L1 in mm	29 mm	Metal sleeve thickness (S1)	0.3 mm
Plastic collar thickness (S2)	0.6 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 6		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H16,0/29 ZH GN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

