

## H2,5/27T ZH GR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Twin wire-end ferrule, 21 mm, 18 mm, grey
Order No.	<a href="#">9037660000</a>
Type	H2,5/27T ZH GR
GTIN (EAN)	4008 190493387
Qty.	100 pc(s).
Packaging	loose

Creation date February 27, 2023 4:58:37 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**H2,5/27T ZH GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.42 g

**Technical data**

Description of article Twin wire end ferrule, grey Version Twin wire-end ferrule

**Wire-end ferrules**

Collar height (A) 8 mm Collar width (B) 4.5 mm

Colour code Telemecanique Conductor cross-section 2.5 mm<sup>2</sup>

Contact surface diameter (D1) 2.8 mm Contact surface length (L2) 18 mm

L1 in mm 27 mm Metal sleeve thickness (S1) 0.15 mm

Plastic collar thickness (S2) 0.4 mm Stripping length 21 mm

Wire connection cross section AWG, max. AWG 14

**Classifications**

ETIM 6.0 EC000005 ETIM 7.0 EC000005

ETIM 8.0 EC000005 ECLASS 9.0 27-40-02-01

ECLASS 9.1 27-40-02-01 ECLASS 10.0 27-40-02-01

ECLASS 11.0 27-40-02-01 ECLASS 12.0 27-40-02-01

**Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

**Downloads**Engineering Data [CAD data – STEP](#)Engineering Data [WSCAD, Zuken E3.S](#)User Documentation [Technical information - EN](#)[Technical information - DE](#)Catalogues [Catalogues in PDF-format](#)

Brochures

**H2,5/27T ZH GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawing**

