

HTF AFK 2.5**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Crimping tools for for turned/stamped contact**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.2mm ² , 2.5mm ²
Order No.	9201040000
Type	HTF AFK 2.5
GTIN (EAN)	4032248419678
Qty.	1 pc(s).

HTF AFK 2.5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	533 g		

Technical data

Description of article	Crimping tool for AFK flat-blade contacts with opened crimping claws		
------------------------	--	--	--

Description of contact

Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	2.5 mm ²
Crimping range, min.	0.2 mm ²	Type of contact	Weidmüller FEKO ZRV

tool data crimping

Crimping profile 1, max.	3.5 mm ²	Crimping profile 1, min.	0.2 mm ²
Crimping profile 2, max.	1 mm ²	Crimping profile 2, min.	0.5 mm ²
Crimping profile 3, max.	2.5 mm ²	Crimping profile 3, min.	1.5 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



Downloads

Catalogues	Catalogues in PDF-format
Brochures	

HTF AFK 2.5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

Similar to illustration

