

**MULTI-STRIPAX AWG****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9202230000</a>
Type	MULTI-STRIPAX AWG
GTIN (EAN)	4032248486168
Qty.	1 pc(s).

## MULTI-STRIPAX AWG

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	250 mm	Width (inches)	9.842 inch
Net weight	520.28 g		

## Technical data

Description of article	Stripping and cutting tool for AWG conductors with PVC and PTFE etc. insulation
------------------------	---

## Stripping tools

Cable type	AWG conductor with PTFE and PVC insulation	Conductor cross-section (cutting capacity)	6 mm <sup>2</sup>
Copper cable - flexible, max.	6 mm <sup>2</sup>	Stripping length, min.	2 mm
Stripping range AWG, max.	16 AWG	Stripping range AWG, min.	26 AWG
max. cutting capacity, fine-strand	6 mm <sup>2</sup>	max. cutting capacity, ribbon	10,2 mm x 4 mm
max. cutting capacity, solid	2.5 mm <sup>2</sup>		

## Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

## Approvals

Approvals



## Downloads

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**MULTI-STRIPAX AWG**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**

