

**STRIPPER PC****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

**General ordering data**

Version	Sheathing strippers
Order No.	<a href="#">9918060000</a>
Type	STRIPPER PC
GTIN (EAN)	4032248359172
Qty.	1 pc(s).

**STRIPPER PC**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Dimensions and weights**

Depth	25 mm	Depth (inches)	0.984 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.921 inch
Net weight	44.4 g		

**Technical data**

Description of article      Cable sheathing stripper for data communication lines with 5-15 mm O.D. ø

**Stripping tools**

Cable type	Data cable / telecommunications and IT	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>	Max. conductor diameter	15 mm
Min. conductor diameter	5 mm	Stripping range AWG, max.	12 AWG
Stripping range AWG, min.	24 AWG	Stripping range, min.	0.25 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

**Environmental Product Compliance**

REACH SVHC      Lead 7439-92-1

**Approvals**

Approvals



**Downloads**

Catalogues      [Catalogues in PDF-format](#)

Brochures

**STRIPPER PC**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

