

MG KIT CA 600

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Version	Testing tools, Multimeter
Order No.	9427460000
Type	MG KIT CA 600
GTIN (EAN)	4032248406197
Qty.	1 Stück

MG KIT CA 600

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	33 mm	Height (inches)	1.299 inch
Width	178 mm	Width (inches)	7.008 inch
Net weight	1,385 g		

Technical data

Version	Multimeter + clamp-on meter
---------	-----------------------------

Measuring and testing devices

AC voltage measuring range	0.2 - 600 V	DC voltage measuring range	0.2 - 600 V
Frequency range, max.	40 kHz	Frequency range, min.	10 kHz
Measured capacitance value, min.	20 µF	Measured current value, max.	600 A
Measured temperature value, max.	750 °C	Measured temperature value, min.	-20 °C
Opening width of current-measuring clamp-on attachment	30 mm	Resistance measuring range, max.	2,000 MΩ
Resistance measuring range, min.	0.2 MΩ	Working temperature, max.	50 °C
Working temperature, min.	0 °C		

Classifications

ETIM 6.0	EC000069	ETIM 7.0	EC000069
ETIM 8.0	EC000069	ECLASS 9.0	27-20-03-01
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-01
ECLASS 11.0	27-20-03-01	ECLASS 12.0	27-20-03-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues [Catalogues in PDF-format](#)

Brochures

MG KIT CA 600

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

