


Loss-Proof Chains


Loss-Proof Wires / Connecting Parts, Mounting Brackets

CAD Data



| Part Number | L 50mm Increment | P | A | d | Reference Applied Load | € Unit Price |
|--------------|---------------------|-----|-----|-----|---------------------------|--------------|
| SCHSP | 100~500 | 5.5 | 2.5 | 1.6 | 9kg | |
| | 550~1000 | | | | | |


⚠ The reference applied load is only a guideline.



| Part Number | L 50mm Increment | P | Reference Applied Load | Accessory (Connector) | € Unit Price |
|--------------|---------------------|----------|---------------------------|-----------------------|--------------|
| Type | D | | | d | l |
| BALLC | 2.3 | 100~500 | 3.3 | 4kg | 3.0 8 |
| | | 550~1000 | | | |
| | 3.2 | 100~500 | 4.4 | 6kg | 4.3 11 |
| | | 550~1000 | | | |

* Depending on the number of links, the actual L dimension may be slightly longer than the specified dimension. (Connecting Parts: A connector is attached.)

⚠ The reference applied load is only a guideline. ⚠ Dimensions of chains and connecting parts are for reference only.



| Part Number | L 50mm Increment | A | B | C | Plate Thickness | Reference Applied Load | € Unit Price |
|-------------|---------------------|----------|------|-----|--------------------|---------------------------|--------------|
| Type | No. | | | | | | |
| CHSP | 4 | 100~500 | 15.5 | 4.2 | 8 | 0.8 | 70kg |
| | | 550~1000 | | | | | |

* Depending on the number of links, the actual L dimension may be slightly longer than the specified dimension. (Please refer to <http://jp.misumi-ec.com/mech/>.)

Connecting parts are not included.) UH: ERL. IN EN/CS/de

⚠ The reference applied load is only a guideline.

Order Example: Part Number - L
CHSP - 600
BALLC.2.3 - 150
CHSP4 - 100


Days to Ship: 8 Days
Express A: 2.00 EUR / piece
P88

⚠ A Express Charge of 5,40 EUR for 3 or more identical pieces.

Volume Discount (⚠ Round down to one Cent.) P87
Quantity 1-19 20-29 30-49 50-99
Discount Rate € Unit Price 5% 10% 18%

⚠ For orders larger than indicated quantity, please request a quotation.




CAD Data



| Part Number | L 50mm Increment | Reference Applied Load | € Unit Price | |
|-------------|---------------------|---------------------------|--------------|---|
| Type | Shape | A | B | C |
| LPWW | A B C | 100~500 | 9kg | |
| | | 550~1000 | | |

⚠ The reference applied load is only a guideline.

Order Example: Part Number - L
LPWW C - 850
8 Days
Days to Ship
Price
Volume Discount (⚠ Round down to one Cent.) P87
Quantity 1-19 20-29 30-49 50-99
Discount Rate € Unit Price 5% 10% 18%
⚠ For orders larger than indicated quantity, please request a quotation.



Order Example: Part Number RWS14
Days to Ship: 8 Days
Express A: 2.00 EUR / piece
P88
⚠ A Express Charge of 5,40 EUR for 3 or more identical pieces.