

Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator flush-type socket, 5-pos., M12, B-coded, rear/screw mounting with M12 thread, with angled solder connection



Key commercial data

package_quantity	10
GTIN	4046356011402

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	125 V
Number of positions	5
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	B - inverse
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder pins
Mounting type	Rear mounting M12 x 1 With locking nut

Material

Inflammability class according to UL 94	HB
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Nickel-plated brass

Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870

Technical data

Material

Sealing material	NBR
------------------	-----

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 2.0	EC001297
ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST / GOST /


Approval details



Drawings

Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870


Drilling diagram



M12 flush-type connector


Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870

Diagram



Attenuation curve of the SACC... male/female connectors


Dimensioned drawing



M12 flush-type connector

Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870


Dimensioned drawing



Panel cutout

Flush-type connector - SACC-DSIV-M12FSB-5CON-L 90 - 1527870

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>