

Valve connectors - SACC-V-3CON-PG9/A-1L 24V - 1527906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Valve connector, 3-pos., type A, 1 LED, without protective circuit, screw connection, cable screw connection Pg9

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 1 |
| GTIN | 4017918981006 |

Technical data

Dimensions

| | |
|--------------------------|---------------|
| External diameter | 6 mm ... 8 mm |
|--------------------------|---------------|

Ambient conditions

| | |
|--|-------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (valve plug) |
| Degree of protection | IP65 |

General

| | |
|-------------------------------------|--|
| Rated current at 40°C | 10 A |
| Rated voltage | 24 V |
| Number of positions | 3 |
| Contact resistance | ≤ 15 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Status display | 1 LED |
| Protective circuit/component | Unwired |
| Surge voltage category | II |
| Pollution degree | 3 |
| Connection method | Screw connection |
| Conductor cross section | 0.34 mm ² ... 1.5 mm ² |
| AWG conductor cross section | 22 ... 16 |

Material

| | |
|--|------|
| Inflammability class according to UL 94 | HB |
| Valve plug contact material | CuSn |
| Valve plug contact surface material | Ni |
| Valve plug contact insert material | PA6 |
| Material housing valve plug | PA6 |

Valve connectors - SACC-V-3CON-PG9/A-1L 24V - 1527906

Technical data

Material

| | |
|------------------|-----|
| Sealing material | NBR |
|------------------|-----|

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140815 |
| eCl@ss 4.1 | 27140815 |
| eCl@ss 5.0 | 27143423 |
| eCl@ss 5.1 | 27143423 |
| eCl@ss 6.0 | 27143423 |
| eCl@ss 7.0 | 27449001 |
| eCl@ss 8.0 | 27449001 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001121 |
| ETIM 3.0 | EC002062 |
| ETIM 4.0 | EC002062 |
| ETIM 5.0 | EC002062 |


UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11 | 31251501 |
| UNSPSC 12.01 | 31251501 |
| UNSPSC 13.2 | 31251501 |

Drawings

Valve connectors - SACC-V-3CON-PG9/A-1L 24V - 1527906

Dimensioned drawing



Circuit diagram

