

Stackable housing - DC-B 6-HD-M25-M - 1602054

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



DUPLICON, aluminum stackable housing for DUPLICON contact inserts, type B6, IP67 protection, with two locking latches, gasket and an M25 cable screw connection thread (without cable screw connection)

Key commercial data

package_quantity	10
GTIN	4046356027755

Technical data

Dimensions

Height	37 mm
--------	-------

Ambient conditions

Degree of protection for housing	IP65
Degree of protection for housing	IP66
Degree of protection for housing	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Design	DC-B6
Housing type	Stackable housing
Color	pearl gray
Locking type	With locking latch
Cable exit	Lateral
Screw connection	None
Type of the screw connection	With M25 thread
Housing material	Aluminum die-cast
Housing surface material	EMC-conductive
Seal material	NBR
Material lock	Stainless steel
Material grip body interlock	PA

classifications

eCl@ss

eCl@ss 4.0	27140816
------------	----------

Stackable housing - DC-B 6-HD-M25-M - 1602054

classifications

eCl@ss

eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

approvals

VDE Gutachten mit Fertigungsüberwachung /

Approval details

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	690 V
Nominal current IN	25 A
mm²/AWG/kcmil	

accessories

Seal

DC-B 6-A-HD-G - 1602326



Stackable housing - DC-B 6-HD-M25-M - 1602054

accessories

Full screw connection

HC-M-KV-M25(11-16) - 1690574



HC-M-KV-M25(14-21) - 1646007



Device marking


EML (26,5X12)R SR - 0816854



Drawings

Stackable housing - DC-B 6-HD-M25-M - 1602054

Dimensioned drawing



Dimensional drawing

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>