

RJ45 male insert - VS-08-ST-H11-RJ45 - 1652716

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



RJ45 pin insert, CAT5e, 8-pos., shielded, IDC connection method, for litz wires AWG 27 ... 26, with strain relief

Ethernet

Key commercial data

package_quantity	5
GTIN	4017918952860

Technical data

Mechanical characteristics

Number of positions	8
Shielded	Yes
Insertion/withdrawal cycles	≥ 750
Connection method	IDC connection technology
Conductor cross section	0.14 mm² ... 0.18 mm² (stranded)
Connection cross section AWG	27 ... 26 (stranded)
Cable exit	Straight

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

Material data

Inflammability class according to UL 94	V2
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Rated current	0.5 A
Surge voltage category	I
Pollution degree	2

RJ45 male insert - VS-08-ST-H11-RJ45 - 1652716

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

accessories

Sleeve housings

VS-08-T-H-RJ45/IP67 - 1652732



VS-08-T-H-RJ45/IP67-BK - 1658671



Bend protection sleeve

RJ45 male insert - VS-08-ST-H11-RJ45 - 1652716

accessories

VS-08-KS-H/GY - 1654743



VS-08-KS-H/GN - 1654756



Crimping tool


VS-CT-RJ45-H - 1653265



Drawings

RJ45 male insert - VS-08-ST-H11-RJ45 - 1652716

Dimensioned drawing



RJ45 male insert

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>