

# Thermal transfer printer - THERMOMARK PRIME - 5148888

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Thermal transfer printer for mobile or stationary use, with integrated "MARKING SYSTEM APP" marking software on board, 7" color touch display and replaceable battery pack. Can be linked to CLIP PROJECT, for printing plastic markers in UCT, US, and UM format.

## Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 1             |
| GTIN             | 4055626041834 |

## Technical data

### General

|           |                      |
|-----------|----------------------|
| Interface | 10/100 Mbps Ethernet |
| Interface | USB 2.0              |
| Weight    | 6.00 kg              |

### Dimensions

|        |           |
|--------|-----------|
| Length | 292.00 mm |
| Height | 122.00 mm |
| Width  | 224.00 mm |

### Connection data

|                 |                 |
|-----------------|-----------------|
| Minimum voltage | 100 V AC        |
| Max. voltage    | 240 V AC        |
| Additional text | 50 Hz ... 60 Hz |

### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50                                                            |
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.1 | 19020205 |
| eCl@ss 8.0 | 19140104 |
| eCl@ss 9.0 | 19140104 |

### ETIM

# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC001672 |
| ETIM 6.0 | EC001672 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 43212108 |
|-------------|----------|

## Approvals

EAC /

### Approval details

|          |
|----------|
| EAC ENEC |
|----------|

## Accessories

### Printing system accessories

TMP/ACCU - 0803668



TMP/EXT.POWER-SUPPLY 100-240V - 0803672



TMP/CHARGER - 0803670

## Thermal transfer printer - THERMOMARK PRIME - 5148888

### Accessories

TMP/ACCU COVER - 0803669



---

TMP/CHARGER CABLE VEHICLE 12V - 0803671

---

TMP BAG - 0803674



---

TMP CASE - 0803675



---

MOBILE BACKPACK - 0803717



---

### Magazine

## Thermal transfer printer - THERMOMARK PRIME - 5148888

### Accessories

TMP-US-MAG1 - 0803341



---

TMP-UCT-MAG1 - 0803342



---

TMP-UCT-MAG2 - 0803343



---

TMP-UCT-MAG3 - 0803344



---

TMP-UCT-MAG4 - 0803345



---

TMP-UCT-MAG5 - 0803347



# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Accessories

---

TMP-UCT-MAG6 - 0803348



---

TMP-UCT-MAG7 - 0803349



---

TMP-UCT-MAG8 - 0803350



---

TMP-UCT-MAG9 - 0803351



---

TMP-UCT-MAG10 - 0803352



# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Accessories

TMP-UCT-MAG11 - 0803353



---

TMP-UCT-MAG12 - 0803354



---

TMP-UCT-MAG13 - 0803355



---

TMP-UCT-MAG14 - 0803356



---

TMP-UCT-MAG15 - 0803357



---

TMP-UCT-MAG16 - 0803358



## Thermal transfer printer - THERMOMARK PRIME - 5148888

### Accessories

---

TMP-UCT-MAG17 - 0803360



---

TMP-UCT-MAG18 - 0803361



---

TMP-UCT-MAG19 - 0803363



---

TMP-UCT-MAG20 - 0803364



---

TMP-UCT-MAG21 - 0803365



# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Accessories

TMP-UCT-MAG22 - 0803366



---

TMP-UCT-MAG25 - 0803369



---

## Ink ribbon

TMP-RIBBON 110 BK 100 - 0803374



---

TMP-RIBBON 110 BK 101 - 0803714



---

TMP-RIBBON 110 BU 100 - 0803378





# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Accessories

TMP-RIBBON 110 GN 100 - 0803380



---

TMP-RIBBON 110 RD 100 - 0803377



---

TMP-RIBBON 110 WH 100 - 0803376



---

TMP-RIBBON 110 YE 100 - 0803379



---

## Accessories

TMP/SDHC FLASH - 0803678

# Thermal transfer printer - THERMOMARK PRIME - 5148888

## Accessories

FD WI-FI - 0803677

---

## Drawings

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>