



SURGE SUPPRESSOR, VARISTOR, AC 24...48V, DC 24...70V, FOR MOTOR CONTACTORS SZ S0,

General technical data:		
product brand name		SIRIUS
Product designation		surge suppressor
Size of contactor		S0
Design of the surge suppressor		with varistor
Ambient temperature		
<ul style="list-style-type: none"> during storage 	°C	-40 ... +80
<ul style="list-style-type: none"> during operation 	°C	-25 ... +60
Control circuit/ Control:		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency		
<ul style="list-style-type: none"> 1 Rated value 	Hz	50
<ul style="list-style-type: none"> 2 Rated value 	Hz	60
Control supply voltage 1		
<ul style="list-style-type: none"> for DC 		
<ul style="list-style-type: none"> <ul style="list-style-type: none"> Initial rated value 	V	24
<ul style="list-style-type: none"> <ul style="list-style-type: none"> Final rated value 	V	70
<ul style="list-style-type: none"> with AC 		
<ul style="list-style-type: none"> <ul style="list-style-type: none"> at 50 Hz Initial rated value 	V	24
<ul style="list-style-type: none"> <ul style="list-style-type: none"> at 50 Hz Final rated value 	V	48
<ul style="list-style-type: none"> <ul style="list-style-type: none"> at 60 Hz Final rated value 	V	48
<ul style="list-style-type: none"> <ul style="list-style-type: none"> at 60 Hz Initial rated value 	V	24
Installation/ mounting/ dimensions:		
mounting position		any

Mounting type		clip-on
Width	mm	30
Height	mm	19
Depth	mm	12

Certificates/ approvals:

Certificate of suitability CE / UL / CSA / CCC

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
--------------------------	---------------------------	-------------------	-------------------



[Special Test Certificate](#)



Shipping Approval



other

[Confirmation](#)

[Environmental Confirmations](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT29261BB00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT29261BB00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT29261BB00&lang=en



last modified:

27.04.2015