



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

## Data

### Electrical data

|                         |      |
|-------------------------|------|
| Rated current (Ex e II) | 12 A |
|-------------------------|------|

### Ratings per IEC/EN 60664-1

|                         |       |
|-------------------------|-------|
| Rated voltage (III / 3) | 800 V |
|-------------------------|-------|

|               |      |
|---------------|------|
| Rated current | 14 A |
|---------------|------|

### Geometrical Data

|       |                    |
|-------|--------------------|
| Width | 27 mm / 1.063 inch |
|-------|--------------------|

|        |                    |
|--------|--------------------|
| Height | 19 mm / 0.748 inch |
|--------|--------------------|



|       |                     |
|-------|---------------------|
| Depth | 4.1 mm / 0.161 inch |
|-------|---------------------|

---

### Material Data

|       |            |
|-------|------------|
| Color | light gray |
|-------|------------|

---

|           |          |
|-----------|----------|
| Fire load | 0.019 MJ |
|-----------|----------|

---

|        |        |
|--------|--------|
| Weight | 2.31 g |
|--------|--------|

---

### Commercial data

|                |     |
|----------------|-----|
| Packaging type | bag |
|----------------|-----|

---

|                   |    |
|-------------------|----|
| Country of origin | DE |
|-------------------|----|

---

|      |               |
|------|---------------|
| GTIN | 4055143696968 |
|------|---------------|

---

|                    |             |
|--------------------|-------------|
| Customs Tariff No. | 85366990990 |
|--------------------|-------------|

---

|               |               |
|---------------|---------------|
| Product Group | 22 (TOPJOB S) |
|---------------|---------------|

---

### Downloads

#### Documentation

##### Bid Text

|          |              |                |          |
|----------|--------------|----------------|----------|
| 2000-408 | Oct 20, 2017 | DOC<br>24.1 kB | Download |
|----------|--------------|----------------|----------|

---

### smartDATA

#### CAD data

|                      |     |          |
|----------------------|-----|----------|
| 3D Download 2000-408 | URL | Download |
|----------------------|-----|----------|

---



## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.