


Data sheet | Item number: 224-114

2-conductor lighting connector; Version for increased continuous service temperature of 120°C

www.wago.com/224-114



Data

Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (II / 2)	400 V
Rated impulse voltage (II / 2)	4 kV
Rated current	24 A
Legend (ratings)	(II / 2) $\triangleq$ Overvoltage category II / Pollution degree 2

Connection data

Connection type (1)	Installation side:
Connection technology	PUSH WIRE®
Number of connection points (connection type)	0
Actuation type	Push-in
Connectable conductor materials	Copper
Solid conductor	1 ... 2.5 mm² / 14 ... 12 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 Inch
Connection type (2)	Lighting side:
Connection technology 2	CAGE CLAMP®
Number of connection points	1
Solid conductor (2)	0.5 ... 2.5 mm² / 20 ... 16 AWG

Fine-stranded conductor (2)	0.5 ... 2.5 mm ² / 20 ... 16 AWG
Total number of connection points	3
Total number of potentials	1
Type of wiring	Side-entry wiring

Geometrical Data

Width	9.5 mm / 0.374 inch
Height	15.5 mm / 0.61 inch
Depth	20.5 mm / 0.807 inch

Material Data

Color	black
Fire load	0.057 MJ
Weight	2.74 g

Commercial data

Country of origin	CH
GTIN	4044918583787
Customs Tariff No.	85369010000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1053495
	VDE VDE Prüf- und Zertifizierungsinstitut	40022792

Ship Approvals

Logo	Approval	Certificate name
	ABS American Bureau of Shipping	15-HG1419918-PDA
	BV Bureau Veritas S.A.	11914/C0 BV
	DNV GL	TAE000015T



Det Norske Veritas, Germanischer Lloyd

UL-Approvals

Logo	Approval	Certificate name
	UL UL International Germany GmbH	CCA-DK No. 2527

Compatible products

General accessories

	Item no.: 249-130 Syringe; Contents: 20 ml Alu-Plus contact paste	www.wago.com/249-130
--	--	--

Downloads

Documentation

Bid Text

224-114	Oct 10, 2017	DOC 25.6 kB	Download
---------	--------------	----------------	----------

smartDATA

CAD data

3D Download 224-114	URL	Download
---------------------	-----	----------

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.