


Data sheet | Item number: 726-671

Ground conductor common potential matrix patchboard; Marking 1-24; with 1 input module incl. end plate; Color of modules: green-yellow; Numbering of modules arranged vertically; for 19" racks; Slimline version



www.wago.com/726-671



Data
Electrical data



Ratings per IEC/EN 60664-1

Rated current	76 A
Rated current (2)	24 A
Legend (ratings)	(III / 3) $\hat{=}$ Overvoltage category III / Pollution degree 3

Connection data

Connection type (1)	Side 1
Connection technology	CAGE CLAMP®
Number of connection points (connection type)	1
Actuation type	Operating tool
Connectable conductor materials	Copper Aluminum
Solid conductor	0.2 ... 16 mm ² / 24 ... 6 AWG
Fine-stranded conductor	0.2 ... 16 mm ² / 24 ... 6 AWG
Strip length	16 ... 17 mm / 0.63 ... 0.67 Inch
Connection type (2)	Side 2
Number of connection points	2
Solid conductor (2)	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor (2)	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length (2)	8 ... 10 mm / 0.31 ... 0.39 Inch
Type of wiring	Front-entry wiring

Geometrical Data

Width	34.6 mm / 1.362 inch
Height	132 mm / 5.197 inch
Depth	80.7 mm / 3.177 inch

Mechanical data

Design	slimline
Marking	Marking 1-24

Material Data

Color	dark gray
Weight	216.704 g

Commercial data


Country of origin	DE
GTIN	4055143623513
Customs Tariff No.	85369010000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1101143
	KEMA/KEUR DEKRA Certification B.V.	71-100850

UL-Approvals



Logo	Approval	Certificate name
	UL UL International Germany GmbH	E45172

Compatible products

General accessories

	Item no.: 726-902 Adaptor	www.wago.com/726-902
--	------------------------------	--

Marking accessories

	Item no.: 209-185 Adaptor	www.wago.com/209-185
	Item no.: 210-612 Marking strips; for self-marking; plain; Self-adhesive	www.wago.com/210-612

check

	Item no.: 210-137 Test plug; 2.3 mm Ø; with 500 mm cable	www.wago.com/210-137
--	---	--

Downloads

Documentation

Bid Text

726-671	Oct 18, 2017	DOC 26.1 kB	Download
---------	--------------	----------------	----------



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.