


**Data sheet | Item number: 726-341**

Matrix patchboard; Marking 1-32; Color of modules: blue; Numbering of modules on sides 1 and 2 arranged vertically and horizontally; for 19" racks; Slimline version; suitable for Ex i applications; 32-pole



[www.wago.com/726-341](http://www.wago.com/726-341)



RoHS  Compliant

BOMcheck.net

Color: ■

**Data**

**Electrical data**

**Ratings per IEC/EN 60664-1**

Rated voltage (III / 3)	500 V
Rated impulse voltage (III / 3)	6 kV
Rated current	10 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3



## Connection data

Connection type (1)	Side 1
Connection technology	CAGE CLAMP®
Number of connection points (connection type)	3
Actuation type	Operating tool
Connectable conductor materials	Copper Aluminum
Solid conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 16 AWG
Fine-stranded conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 16 AWG
Strip length	8 ... 10 mm / 0.31 ... 0.39 Inch
Connection type (2)	Side 2
Number of connection points	3
No. of poles	32
Type of wiring	Front-entry wiring

## Geometrical Data

Width	34.6 mm / 1.362 inch
Height	132 mm / 5.197 inch
Depth	36.5 mm / 1.437 inch

## Mechanical data

Design	slimline
Marking	Marking 1-32

## Material Data

Color	dark gray
Fire load	2.499 MJ
Weight	142.4 g

## Commercial data

Country of origin	DE
GTIN	4044918456104
Customs Tariff No.	85369010000

## Approvals / Certificates

### Country specific Approvals

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1101143




KEMA/KEUR  
DEKRA Certification B.V.

71-100850






## UL-Approvals

Logo	Approval	Certificate name
	UL UL International Germany GmbH	E45172

## Compatible products



## General accessories

	<b>Item no.: 726-902</b> Adaptor	<a href="http://www.wago.com/726-902">www.wago.com/726-902</a>
	<b>Item no.: 726-903</b> Additional module for matrix patchboards; for snap-on fixing to the lower fixing element; Additional module with contact to mounting frame	<a href="http://www.wago.com/726-903">www.wago.com/726-903</a>
	<b>Item no.: 726-904</b> Additional module for matrix patchboards; for snap-on fixing to the lower fixing element; insulated; Additional module	<a href="http://www.wago.com/726-904">www.wago.com/726-904</a>




## check

	<b>Item no.: 210-137</b> Test plug; 2.3 mm Ø; with 500 mm cable	<a href="http://www.wago.com/210-137">www.wago.com/210-137</a>
--	--	--

## ferrule

	<b>Item no.: 216-123</b> Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; uninsulated; electro-tin plated	<a href="http://www.wago.com/216-123">www.wago.com/216-123</a>
	<b>Item no.: 216-202</b> Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated	<a href="http://www.wago.com/216-202">www.wago.com/216-202</a>

## Marking accessories

	<b>Item no.: 209-185</b> Adaptor	<a href="http://www.wago.com/209-185">www.wago.com/209-185</a>
	<b>Item no.: 209-500/209-035</b> WSB marking card; as card; MARKED; X (100x); not stretchable; Horizontal marking; snap-on type	<a href="http://www.wago.com/209-500/209-035">www.wago.com/209-500/209-035</a>
	<b>Item no.: 209-501</b> WSB marking card; as card; not stretchable; plain; snap-on type	<a href="http://www.wago.com/209-501">www.wago.com/209-501</a>



**Item no.: 209-501/000-002**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-002](http://www.wago.com/209-501/000-002)



**Item no.: 209-501/000-005**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-005](http://www.wago.com/209-501/000-005)



**Item no.: 209-501/000-006**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-006](http://www.wago.com/209-501/000-006)



**Item no.: 209-501/000-007**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-007](http://www.wago.com/209-501/000-007)



**Item no.: 209-501/000-012**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-012](http://www.wago.com/209-501/000-012)



**Item no.: 209-501/000-017**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-017](http://www.wago.com/209-501/000-017)



**Item no.: 209-501/000-023**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-023](http://www.wago.com/209-501/000-023)



**Item no.: 209-501/000-024**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-501/000-024](http://www.wago.com/209-501/000-024)



**Item no.: 209-502**  
WSB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type

[www.wago.com/209-502](http://www.wago.com/209-502)



**Item no.: 209-566**  
WSB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type

[www.wago.com/209-566](http://www.wago.com/209-566)



**Item no.: 210-612**  
Marking strips; for self-marking; plain; Self-adhesive

[www.wago.com/210-612](http://www.wago.com/210-612)



**Item no.: 726-905**  
Adaptor

[www.wago.com/726-905](http://www.wago.com/726-905)

#### Insulation stop



**Item no.: 726-901**  
Insulation stop; 0.08 - 0.2 mm<sup>2</sup> "s" (0.14 mm<sup>2</sup> "f-st"); 4 x 3 pieces/strip

[www.wago.com/726-901](http://www.wago.com/726-901)



**Item no.: 726-906**  
Insulation stop; 0.25 mm<sup>2</sup> "s"; 0.14 - 0.25 mm<sup>2</sup> "f-st"; 4 x 3 pieces/strip

[www.wago.com/726-906](http://www.wago.com/726-906)



**Item no.: 726-907**  
Insulation stop; 0.25 - 0.5 mm<sup>2</sup> "s+f-st"; 4 x 3 pieces/strip

[www.wago.com/726-907](http://www.wago.com/726-907)

#### Jumper

**Item no.: 709-107**



Wire commoning chain; insulated; 32 connections

[www.wago.com/709-107](http://www.wago.com/709-107)

---

tools



Item no.: 210-719

Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm

[www.wago.com/210-719](http://www.wago.com/210-719)

---

Downloads

Documentation

Bid Text

726-341	Oct 18, 2017	DOC 26.1 kB	Download
---------	--------------	----------------	----------

---

smartDATA

CAD data

3D Download 726-341	URL	Download
---------------------	-----	----------

Subject to changes.