

Technical Datasheet

Create Date: 06.06.2016 - Page 1/1

Rust Loosener

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.



6-fold function

WEICON Rust Loosener's six-fold function makes it indispensible for repairs, maintenance and servicing. Thanks to its excellent creeping capacity, WEICON Rust Loosener reaches even the smallest cavities.

WEICON Rust Loosener loosens rusted and stiff parts, screws, bolts, joints and hinges, permanently protects against corrosion and oxidation, durably lubricates sliding surfaces, cleans and cares for metallic surfaces and mechanical parts and is temperature resistant from -20 °C to +150 °C (-4 to +302 °F).

Technical data

Colour	beige
Odour	Petroleum
Temperature resistance	-20 bis +150 °C
Shelf life min.	24 months
Special features	6-fold function
Suitable for use with	Pump dispenser, WSD 400 and WPS 1500

Processing

Richly brush on or spray on (e.g. with an Air Pressure Can). Allow to react for a short time. Repeat if necessary.

Storage

Keep in closed original container. Protect from direct solar radiation. Storage temperature may not exceed +50°C.

Store container at cool and aired place. Store in a dry place.

Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

WEICON GmbH & Co. KG (Headquarter)

WEICON Middle East L.L.C.

Königsberger Str. 255 · DE-48157 Münster P.O. Box 84 60 · DE-48045 Münster Germany

 Tel.
 +49 (0) 251 / 93 22-0

 Fax
 +49 (0) 251 / 93 22-244

 Fax
 +49 (0) 251 / 93 22-233 Export

 www.weicon.de · info@weicon.de

Jebel Ali Ind Area 3 · P.O. Box 118 216 Dubai · U.A.E

Phone +971 4 880 25 05 Fax +971 4 880 25 09 Mobile +971 50 545 99 83 www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20 Kitchener · Ontario · N2E 2C3 Canada

Phone +1 519 896 5252 Fax +1 519 896 5254 Cell +1 519 590 5168 www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi Arifağa Sokak No: 29 Kat: 3 34530 Yenibosna – Istanbul Turkey www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1 547176 Budiu Mic (Targu Mures) www.weicon.com · office@weicon.com