

Smoothing Agent



simple smoothing of many sealants

The Smoothing Agent is a transparent mixture of non-ionic surface activators. Applying it makes it possible to easily and cleanly smooth off all WEICON elastic adhesives and sealants such as silicone, MS polymers, polyurethane, etc. prior to skin formation.

Technical data

Basis	Mixture of nonionic surface activators
Colour	colourless, transparent
Density	1,00 g/cm ³
Consumption	20 - 40 ml/m ²
Processing temperature	+10 bis +40 °C

Suitable for:

WEICON MS-Polymers

- Flex 310 M Classic
- Flex 310 M Crystal
- Flex 310 M Stainless-Steel
- Flex 310 M Super-Tack
- Flex 310 M 2 K
- Flex+bond
- Solar-Flex
- Speed-Flex
- Aqua-Flex

WEICON Polyurethanes

- Flex 310 PU
- Flex 310 RLT

WEICON Silicone

- Silicon A
- Silicon N
- HT 300
- Black-Seal

Processing

Shake contents before use. Spray the undiluted Smoothing Agent generously onto the joint or a smoothing spatula and smooth the joint. Pull off the protruding sealant and remove immediately. Wash off redundant smoothing agent straightaway with clear water.

Storage

Keep tightly closed in the original packaging. Protect from direct sunlight. The storage temperature must not exceed +50°C. Keep container in a cool, well-ventilated location. Store in a dry and frost-free place. Close opened containers tightly and use up within a short time.

Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
Fax +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada

Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – İstanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1
547176 Budiu Mic (Targu Mures)
www.weicon.com · office@weicon.com