

Slot Covers

Resin, Soft Resin, Rubber/ Elastomer, PVC

1.5m Set is now available. 13% cheaper than existing 2m products.

Slot Covers

| Type | Material | Heat Resistant Temperature (°C) |
|---------------|--|---------------------------------|
| HSCA HSCAS | Polyethylene (Black, Light Gray, Yellow, Red) | -40~80 |
| HSCL HSCLS | Low Density Polyethylene (Black, Light Gray) | -40~80 |
| HSCB HSCV | Styrene Type Elastomer (Shore A60) (Light Gray) PVC (Black, Light Gray) | -75~130 0~60 |

HSCA (Polyethylene) and HSCL (Low density polyethylene) may expand or contract about 0.5% as temperature changes by 20°C.

RoHS10

Slot Covers (Resin / Soft Resin)

For HFS5 Series
HSCA5
HSCL5
HSCAS5
HSCLS5

For HFS6 Series
HSCA6
HSCL6
HSCAS6
HSCLS6

For HFS8 Series
HSCA8
HSCL8
HSCAS8
HSCLS8

For HFS8-45 Series
HSCA845
HSCL845

Slot covers are used in reverse as Plate Covers. HFS5 can hold a 3mm plate, HFS6, HFS8 and HFS8-45 can hold a 5mm plate.
HSCL (soft resin) is made of softer material compared to HSCA (resin). Post assembly insertion is easy. (For details, see lower section of P.773.)

Slot Covers (Elastomer)

For HFS5 Series
HSCB5

For HFS6 Series
HSCB6

For HFS8, HFS8-45 Series
HSCB8

Slot Cover (Soft PVC)

For HFS5 Series
HSCV5

For HFS6 Series
HSCV6

For HFS8, HFS8-45 Series
HSCV8

Since HSCV is a Dust Resistant type, it is more difficult to install than the Standard type (HSCA).

| Part Number | | No. | Color | Length m | Extrusion (Series) | Unit Price | |
|----------------------|-----|-----|--------------|-------------|-----------------------|--------------|---------|
| Type | | | | | | 1 ~ 8 pc(s). | 9 ~ 100 |
| HSCA (Resin) | 5 | B | (Black) | 2 | HFS5 | | |
| | 6 | S | (Light Gray) | | HFS6 | | |
| | 8 | Y | (Yellow) | | HFS8 | | |
| | 845 | R | (Red) | | HFS8-45 | | |
| HSCL (Soft Resin) | 5 | B | (Black) | 2 | HFS5 | | |
| | 6 | S | (Light Gray) | | HFS6 | | |
| | 8 | S | (Light Gray) | | HFS8 | | |
| | 845 | S | (Light Gray) | | HFS8-45 | | |
| HSCB (Elastomer) | 5 | S | (Light Gray) | 2.7 | HFS5 | | |
| | 6 | | | | HFS6 | | |
| | 8 | | | | HFS8 | | |
| | 845 | | | | HFS8-45 | | |
| HSCV (Soft PVC) | 5 | B | (Black) | 5 | HFS5 | | |
| | 6 | | | | HFS6 | | |
| | 8 | | | | HFS8 | | |
| | 845 | S | (Light Gray) | | HFS8-45 | | |

| Part Number | | No. | Color | SET | Length m | Extrusion (Series) | Unit Price |
|-----------------------|---|-----|--------------|------|-------------|-----------------------|------------|
| Type | | | | | | | |
| HSCAS (Resin) | 5 | B | (Black) | SET5 | 1.5 | HFS5 | |
| | 6 | S | (Light Gray) | | | HFS6 | |
| | 8 | S | (Light Gray) | | | HFS8 | |
| HSCLS (Soft Resin) | 5 | B | (Black) | SET5 | 1.5 | HFS5 | |
| | 6 | S | (Light Gray) | | | HFS6 | |
| | 8 | S | (Light Gray) | | | HFS8 | |

Can be cut with a utility knife.
Length is 1.5m.
Prices in the table are the sum of 5 pcs. prices.

| Part Number | | No. | Color | SET | Length m | Extrusion (Series) | Unit Price |
|----------------------|-----|-----|--------------|--------|-------------|-----------------------|------------|
| Type | | | | | | | |
| HSCA (Resin) | 5 | B | (Black) | SET100 | 2 | HFS5 | |
| | 6 | S | (Light Gray) | | | HFS6 | |
| | 8 | Y | (Yellow) | | | HFS8 | |
| | 845 | R | (Red) | | | HFS8-45 | |
| HSCL (Soft Resin) | 5 | B | (Black) | SET100 | 2 | HFS5 | |
| | 6 | S | (Light Gray) | | | HFS6 | |
| | 8 | S | (Light Gray) | | | HFS8 | |
| | 845 | S | (Light Gray) | | | HFS8-45 | |

Length is 2m.
Prices in the table are the sum of 100 pc. prices.

Price Difference between Single Item and Set
(Ex.) Slot Cover Material: Resin, Color: Black

| Part Number | Quantity | Length (m) | Unit Price | Meter Unit Price |
|-----------------|----------|------------|------------|------------------|
| HSCAS-B | 1 | 2 | | |
| HSCAS5-B-SET5 | 5 | 1.5 | | |
| HSCAS5-B-SET100 | 100 | 2 | | |

| Part Number | Color | SET |
|-------------|-------|--------|
| HSCA6 | B | |
| HSCAS5 | S | SET5 |
| HSCA5 | B | SET100 |

Attachment Method

Example
• Slot Cover Example
• Plate Holder Example

Features of HSCL and HSCLS (Soft Resin)
It is softer than HSCA or HSCAS (Resin).
It is easy to insert into a slot and can be easily cut with scissors.

Comparison of HSCA/HSCAS (Resin) and HSCL/HSCLS (Soft Resin)

| Part Number | HSCA, HSCAS | HSCL, HSCLS |
|------------------|-------------|-------------|
| Deflection mm | 0.5 | 2 |

[Measuring Method]
Put HSCA/HSCAS and HSCL/HSCLS longitudinally and apply weight of 500g, then measure the deflection.

Slot Covers

Sponge, Aluminum Low Profile, Aluminum

Sponge Type

Slot Covers (Sponge)

For HFS5 Series
HSCJ5
HSCJF5

For HFS8, HFS8-45 Series
HSCJ8
HSCJF8

For HFS6 Series
HSCJ6
HSCJF6

| Type | Material | Color | Heat Resistance Temperature |
|-------|---------------------------|-----------|-----------------------------|
| HSCJ | Chloroprene Rubber Sponge | Black | 100°C |
| HSCJF | Silicon Rubber Sponge | Vermilion | 200°C |

Sponge type of slot covers can be used for a curved aluminum extrusions on P.534, 582, 639.

Standard Length (Sponge)

| Part Number | | No. | Color | Length m | Extrusion (Series) | Unit Price | |
|-------------|---|-----|---------|-------------|-----------------------|--------------|--------|
| Type | | | | | | 1 ~ 8 pc(s). | 9 ~ 50 |
| HSCJ | 5 | B | (Black) | 12 | HFS5 | | |
| | 6 | | | | HFS6 | | |
| | 8 | | | | HFS8 HFS8-45 | | |

For orders larger than indicated quantity, please check with WOS.

| Part Number | Color | Length |
|-------------|-------|--------|
| HSCJ6 | B | 12 |
| HSCJF8 | R | 500 |

Configurable Length (Sponge)

| Part Number | | No. | Color | Length 1mm Increment | Extrusion (Series) | Unit Price/m | |
|-------------|---|-----|---------|-------------------------|-----------------------|---------------|---------------|
| Type | | | | | | 1 ~ 50 pc(s). | 1 ~ 50 pc(s). |
| HSCJF | 5 | B | (Black) | 100~3000 | HFS5 | | |
| | 6 | | | | HFS6 | | |
| | 8 | | | | HFS8 HFS8-45 | | |

For orders larger than indicated quantity, please check with WOS.

Aluminum Low Profile

Aluminum Type

| Type | Material | Surface Treatment |
|------------|---------------------------------|-------------------|
| HSCZ, HSCM | Aluminum (EN AW-6063-T5 Equiv.) | Anodize |

RoHS10

Slot Covers (Aluminum Low Profile)

For HFS5 Series
HSCZ5

For HFS6 Series
HSCZ6

For HFS8 Series
HSCZ8

For HFS8-45 Series
HSCZ845

Slot Covers (Aluminum)

For HFS5 Series
HSCM5

For HFS6 Series
HSCM6

For HFS8, HFS8-45 Series
HSCM8

Configurable Length (Aluminum Low Profile)

| Part Number | | Length 1mm Increment | Extrusion (Series) | Unit Price | | Unit Price/m | |
|-------------|-----|-------------------------|-----------------------|-----------------|---------------|---------------|---------------|
| Type | | | | Less than 300mm | 300mm or more | 300mm or more | 300mm or more |
| HSCZ | 5 | 50~2500 | HFS5 | 1 ~ 9 pc (s). | 10~19 | 20~50 | 1 ~ 9 pc (s). |
| | 6 | | HFS6 | | | | |
| | 8 | | HFS8 | | | | |
| | 845 | | HFS8-45 | | | | |

| Part Number | Length |
|-------------|--------|
| HSCZ5 | 100 |
| HSCM5 | 100 |

Configurable Length (Aluminum)

| Part Number | | Length 1mm Increment | Extrusion (Series) | Unit Price/m | |
|-------------|---|-------------------------|-----------------------|---------------|---------------|
| Type | | | | 1 ~ 50 pc(s). | 1 ~ 50 pc(s). |
| HSCM | 5 | 50~4000 | HFS5 | | |
| | 6 | | HFS6 | | |
| | 8 | | HFS8 HFS8-45 | | |

Example
• Example of Pre-Assembling Insertion
• Example of Post-Assembling Insertion

Possible to install on assembled extrusion frames. (Insert them by using a wooden hammer or a resin hammer.)