




|                                                                                                            |      |           |      |                                           |  |                                    |                                                                                                                                        |          |
|------------------------------------------------------------------------------------------------------------|------|-----------|------|-------------------------------------------|--|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|----------|
| UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN MILLIMETERS<br>SURFACE FINISH:<br>TOLERANCES: ISO 2768 mk |      |           |      | FINISH:<br><br>Electroless Nickel Plating |  | DEBURR AND<br>BREAK SHARP<br>EDGES | DO NOT SCALE DRAWING                                                                                                                   | REVISION |
| DRAWN                                                                                                      | NAME | SIGNATURE | DATE |                                           |  |                                    | <div></div> <div>Rotary shaft</div> <div>A3</div> |          |
| CHK'D                                                                                                      |      |           |      |                                           |  |                                    |                                                                                                                                        |          |
| APPV'D                                                                                                     |      |           |      |                                           |  |                                    |                                                                                                                                        |          |
| MFG                                                                                                        |      |           |      |                                           |  |                                    |                                                                                                                                        |          |
| Q.A                                                                                                        |      |           |      |                                           |  |                                    |                                                                                                                                        |          |
|                                                                                                            |      |           |      |                                           |  | MATERIAL:<br>EN 1.1191 Equiv       | SCALE: 1:1                                                                                                                             |          |
|                                                                                                            |      |           |      |                                           |  | WEIGHT:                            | SHEET 1 OF 1                                                                                                                           |          |