

FAG



★ 6032-M

Deep groove ball bearing

Schaeffler ID:
0167186900000Deep groove ball bearing 60...-M, single
row, solid brass cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	6,1 kg	Weight

Main Dimensions & Performance Data

d	160 mm	Bore diameter
D	240 mm	Outside diameter
B	38 mm	Width
C_r	142.000 N	Basic dynamic load rating, radial
C_{0r}	136.000 N	Basic static load rating, radial
C_{ur}	6.000 N	Fatigue load limit, radial
n_G	4.800 1/min	Limiting speed
n_{gr}	3.750 1/min	Reference speed

Dimensions

r_{\min}	2,1 mm	Minimum chamfer dimension
D_1	214,6 mm	Shoulder diameter outer ring
d_1	186,2 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a \min}$	170,2 mm	Minimum diameter shaft shoulder
$D_{a \max}$	229,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum fillet radius

Calculation factors

f_0	16	Calculation factor
-------	----	--------------------