



FAG


## ★ 608

## Deep groove ball bearing

Schaeffler ID:  
0383906470000Deep groove ball bearing 60, single row,  
steel sheet metal cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	12 g	Weight

## Main Dimensions &amp; Performance Data

d	8 mm	Bore diameter
D	22 mm	Outside diameter
B	7 mm	Width
$C_r$	3.297 N	Basic dynamic load rating, radial
$C_{0r}$	1.368 N	Basic static load rating, radial
$C_{ur}$	71 N	Fatigue load limit, radial
$n_G$	47.000 1/min	Limiting speed
$n_{gr}$	31.500 1/min	Reference speed

## Dimensions

$r_{\min}$	0,3 mm	Minimum chamfer dimension
$D_1$	18 mm	Shoulder diameter outer ring
$d_1$	12,14 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a\min}$	10 mm	Minimum diameter shaft shoulder
$D_{a\max}$	20 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,3 mm	Maximum fillet radius

## Calculation factors

$f_0$	12,4	Calculation factor
-------	------	--------------------