

FAG



★ 6040-M

Deep groove ball bearing

Schaeffler ID:
0167187550000Deep groove ball bearing 60...-M, single
row, solid brass cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	200 °C	Operating temperature max.
	14,412 kg	Weight

Main Dimensions & Performance Data

d	200 mm	Bore diameter
D	310 mm	Outside diameter
B	51 mm	Width
C_r	231.000 N	Basic dynamic load rating, radial
C_{0r}	243.000 N	Basic static load rating, radial
C_{ur}	9.900 N	Fatigue load limit, radial
n_G	3.650 1/min	Limiting speed
n_{gr}	3.000 1/min	Reference speed

Dimensions

r_{\min}	2,1 mm	Minimum chamfer dimension
D_1	276,3 mm	Shoulder diameter outer ring
d_1	234,8 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a\min}$	210,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	299,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,1 mm	Maximum fillet radius

Calculation factors

f_0	15,6	Calculation factor
-------	------	--------------------