



FAG



## ★ 61908

## Deep groove ball bearing

Schaeffler ID:  
0097866000000Deep groove ball bearing 619, single row,  
steel sheet metal cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	0,117 kg	Weight

## Main Dimensions &amp; Performance Data

d	40 mm	Bore diameter
D	62 mm	Outside diameter
B	12 mm	Width
$C_r$	14.500 N	Basic dynamic load rating, radial
$C_{0r}$	9.900 N	Basic static load rating, radial
$C_{ur}$	590 N	Fatigue load limit, radial
$n_G$	15.800 1/min	Limiting speed
$n_{gr}$	10.000 1/min	Reference speed

## Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$D_1$	55,1 mm	Shoulder diameter outer ring
$d_1$	46,9 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a\min}$	43,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	58,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,6 mm	Maximum fillet radius

## Calculation factors

$f_0$	15,5	Calculation factor
-------	------	--------------------