

FAG



## ★ 6324-M

Deep groove ball bearing

Schaeffler ID:  
0191119400000Deep groove ball bearing 63...-M, single  
row, solid brass cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	14,78 kg	Weight

## Main Dimensions &amp; Performance Data

d	120 mm	Bore diameter
D	260 mm	Outside diameter
B	55 mm	Width
$C_r$	225.000 N	Basic dynamic load rating, radial
$C_{0r}$	195.000 N	Basic static load rating, radial
$C_{ur}$	9.800 N	Fatigue load limit, radial
$n_G$	4.550 1/min	Limiting speed
$n_{gr}$	3.800 1/min	Reference speed

## Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
$D_1$	215 mm	Shoulder diameter outer ring
$d_1$	165 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a \min}$	134 mm	Minimum diameter shaft shoulder
$D_{a \max}$	246 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,5 mm	Maximum fillet radius

## Calculation factors

$f_0$	13,8	Calculation factor
-------	------	--------------------