

FAG



## ★ 1306-TVH

Self-aligning ball bearing

Schaeffler ID:  
0167006940000Self-aligning ball bearing 13..-TVH, plastic  
cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	0,384 kg	Weight

## Main Dimensions &amp; Performance Data

d	30 mm	Bore diameter
D	72 mm	Outside diameter
B	19 mm	Width
$r_{\min}$	1,1 mm	Minimum chamfer dimension
$C_r$	21.700 N	Basic dynamic load rating, radial
$C_{0r}$	6.300 N	Basic static load rating, radial
$C_{ur}$	400 N	Fatigue load limit, radial
$n_G$	11.100 1/min	Limiting speed
$n_{gr}$	8.700 1/min	Reference speed

## Dimensions

$D_1$	58,9 mm	Shoulder diameter outer ring
$d_1$	45 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a \min}$	37 mm	Minimum diameter shaft shoulder
$D_{a \max}$	65 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum fillet radius

## Calculation factors

e	0,26	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	2,41	Dynamic axial load factor
$Y_2$	3,72	Dynamic axial load factor
$Y_0$	2,52	Static axial load factor