

FAG

## ★ 2209-TVH



Self-aligning ball bearing

Schaeffler ID:  
0167029210000

Self-aligning ball bearing 22...-TVH, plastic cage

★ Preferred product

## Technical information



## Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	120 °C	Operating temperature max.
	0,517 kg	Weight

## Main Dimensions &amp; Performance Data

d	45 mm	Bore diameter
D	85 mm	Outside diameter
B	23 mm	Width
$r_{min}$	1,1 mm	Minimum chamfer dimension
$C_r$	28.500 N	Basic dynamic load rating, radial
$C_{0r}$	9.000 N	Basic static load rating, radial
$C_{ur}$	570 N	Fatigue load limit, radial
$n_G$	8.600 1/min	Limiting speed
$n_{gr}$	7.800 1/min	Reference speed

## Dimensions

$D_1$	75,4 mm	Shoulder diameter outer ring
$d_1$	59 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a min}$	52 mm	Minimum diameter shaft shoulder
$D_{a max}$	78 mm	Maximum diameter of housing shoulder
$r_{a max}$	1 mm	Maximum fillet radius

## Calculation factors

e	0,26	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	2,43	Dynamic axial load factor
$Y_2$	3,76	Dynamic axial load factor
$Y_0$	2,55	Static axial load factor