

FAG



## ★ 2203-2RS-TVH

Self-aligning ball bearing

Schaeffler ID:  
0167026620000Self-aligning ball bearing 22...-2RS-TVH,  
seals, plastic cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.
	0,095 kg	Weight

## Main Dimensions &amp; Performance Data

d	17 mm	Bore diameter
D	40 mm	Outside diameter
B	16 mm	Width
$r_{\min}$	0,6 mm	Minimum chamfer dimension
$C_r$	8.100 N	Basic dynamic load rating, radial
$C_{0r}$	2.010 N	Basic static load rating, radial
$C_{ur}$	128 N	Fatigue load limit, radial
$n_G$	11.300 1/min	Limiting speed

## Dimensions

$D_2$	34,3 mm	Caliber diameter outer ring
$d_2$	21,6 mm	Caliber diameter inner ring

## Mounting dimensions

$d_{a\min}$	21,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	35,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,6 mm	Maximum fillet radius

## Calculation factors

e	0,33	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	1,93	Dynamic axial load factor
$Y_2$	2,98	Dynamic axial load factor
$Y_0$	2,02	Static axial load factor