



FAG

## ★ 11210-TVH

Self-aligning ball bearing

Schaeffler ID:  
0167001800000

Self-aligning ball bearing 112...-TVH, plastic cage

★ Preferred product

## Technical information

## Main Dimensions &amp; Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	20 mm	Width, outer ring
B <sub>i</sub>	58 mm	Width, inner ring
r <sub>min</sub>	1,1 mm	Minimum chamfer dimension
C <sub>r</sub>	22.900 N	Basic dynamic load rating, radial
C <sub>0r</sub>	8.100 N	Basic static load rating, radial
C <sub>ur</sub>	520 N	Fatigue load limit, radial
n <sub>G</sub>	8.700 1/min	Limiting speed
n <sub>gr</sub>	7.700 1/min	Reference speed
	0,85 kg	Weight

## Dimensions

D <sub>1</sub>	77,1 mm	Shoulder diameter outer ring
d <sub>1</sub>	62,7 mm	Shoulder diameter inner ring
b	7 mm	Width retaining slot
t	9 mm	Height retaining slot

## Mounting dimensions

D <sub>a max</sub>	83 mm	Maximum diameter of housing shoulder
r <sub>a max</sub>	1 mm	Maximaler Hohlkehlradius

## Calculation factors

e	0,2	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y <sub>1</sub>	3,15	Dynamic axial load factor
Y <sub>2</sub>	4,87	Dynamic axial load factor
Y <sub>0</sub>	3,3	Static axial load factor

