

FAG


★ 2208-K-2RS-TVH-C3

Self-aligning ball bearing

Schaeffler ID:
0384725700030Self-aligning ball bearing 22..-K-2RS-TVH,
tapered bore taper 1:12, seals, plastic
cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.
	0,486 kg	Weight

Main Dimensions & Performance Data


d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	23 mm	Width
r_{\min}	1,1 mm	Minimum chamfer dimension
C_r	19.400 N	Basic dynamic load rating, radial
C_{0r}	6.500 N	Basic static load rating, radial
C_{ur}	415 N	Fatigue load limit, radial
n_G	4.950 1/min	Limiting speed

Dimensions

D_2	70,3 mm	Caliber diameter outer ring
d_2	49,2 mm	Caliber diameter inner ring

Mounting dimensions

$d_{a\min}$	47 mm	Minimum diameter shaft shoulder
$d_{a\max}$	52 mm	Maximum diameter shaft shoulder
$D_{a\max}$	73 mm	Maximum diameter of housing shoulder
$d_{b\min}$	43 mm	Minimum cavity diameter of the sleeve
$B_{a\min}$	5 mm	Minimum cavity width of the sleeve
$r_{a\max}$	1 mm	Maximum fillet radius



Calculation factors

e	0,22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H308	Adapter sleeve
Y ₁	2,91	Dynamic axial load factor
Y ₂	4,51	Dynamic axial load factor
Y ₀	3,05	Static axial load factor