

FAG



## ★ 1201-TVH

Self-aligning ball bearing

Schaeffler ID:  
0167002360000Self-aligning ball bearing 12..-TVH, plastic  
cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	0,04 kg	Weight

## Main Dimensions &amp; Performance Data

$d$	12 mm	Bore diameter
$D$	32 mm	Outside diameter
$B$	10 mm	Width
$r_{\min}$	0,6 mm	Minimum chamfer dimension
$C_r$	5.700 N	Basic dynamic load rating, radial
$C_{0r}$	1.270 N	Basic static load rating, radial
$C_{ur}$	80 N	Fatigue load limit, radial
$n_G$	28.000 1/min	Limiting speed
$n_{gr}$	21.300 1/min	Reference speed

## Dimensions

$D_1$	25,1 mm	Shoulder diameter outer ring
$d_1$	18,2 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a \min}$	16,2 mm	Minimum diameter shaft shoulder
$D_{a \max}$	27,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	0,6 mm	Maximum fillet radius

## Calculation factors

$e$	0,37	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	1,68	Dynamic axial load factor
$Y_2$	2,61	Dynamic axial load factor
$Y_0$	1,76	Static axial load factor