



FAG

★ B7007-C-T-P4S-UL

Spindle bearing

Schaeffler ID:
0191504580000

★ Preferred product

Spindle bearings B70...-C, adjusted, in pairs or sets, contact angle $\alpha = 15^\circ$, restricted tolerances

Technical information



Temperature range


T_{\min}	-30 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.
	0,002 kg	Weight

Main Dimensions & Performance Data

d	35 mm	Bore diameter
D	62 mm	Outside diameter
B	14 mm	Width
C_r	19.300 N	Basic dynamic load rating, radial
C_{0r}	9.600 N	Basic static load rating, radial
C_{ur}	1.020 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	24.000 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	38.000 1/min	Limiting speed for oil lubrication

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
$r_{1 \min}$	1 mm	Minimum chamfer dimension
α	15 °	Contact angle



Mounting dimensions

d_a	41 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	56 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,3 mm	Maximum recess radius
$E_{tk \min}$	44,5 mm	Minimum diameter injection pitch
$E_{tk \max}$	46,3 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	44,5 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	46,3 mm	Maximum diameter injection pitch
a	13,5 mm	Distance between the apexes of the pressure cones

Additional information

F_{VL}	95 N	Preload force light
F_{VM}	321 N	Preload force medium
F_{VH}	649 N	Preload force heavy
K_{aEL}	296 N	Lift-off force light
K_{aEM}	1.087 N	Lift-off force medium
K_{aEH}	2.357 N	Lift-off force heavy
c_{aL}	38,3 N/ μm	Axial rigidity light
c_{aM}	66,6 N/ μm	Axial rigidity medium
c_{aH}	95,8 N/ μm	Axial rigidity heavy